

Product data sheet

Characteristics

P40MD20

Clipsal Pro Series, Switch Mechanism, 1-Way,
Double Pole, 250V, 20A, X

Main

Range	Pro Series
Product or component type	Switch
Quantity per set	Set of 20

Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	2-pole 1-way
Rated current	20 A
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene)
Fixing mode	By clips
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	23 mm
Width	23 mm
Depth	33 mm
Net weight	0.016 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.2 cm
Package 1 Length	2.4 cm
Package 1 Weight	16.98 g