

## Product data sheet

### Characteristics

# PDL395CSG

Connected Socket, Iconic, BLE default mode,  
Twin horizontal, 10 A, 240 V, Grid



### Main

|                           |                                      |
|---------------------------|--------------------------------------|
| Range compatibility       | PDL mounting bracket<br>PDL wall box |
| Product brand             | PDL                                  |
| Range                     | Iconic                               |
| Product or component type | Socket-outlet                        |


### Complementary

|                                |  |
|--------------------------------|--|
| Device presentation            | Complete product   |
| Socket-outlet type             | Twin switched socket-outlet  |
| [Ue] rated operational voltage | 240 V AC 50 Hz   |
| Colour tint                    | White  |
| Surface finish                 | Matt   |
| Local signalling               | LED  |
| Control type                   | Rocker on/off switching<br>By mobile application                                       |
| Software name                  | Wiser by SE App  |
| Module configuration           | Programmed with touch switch   |
| Rated current                  | 10 A   |
| Technology type                | Bluetooth low energy default<br>Zigbee   |
| Memory description             | Backup memory - date and time for 6 h<br>Backup memory - program for indefinite period |
| Material                       | Plastic  |
| Type of installation           | Indoor installation  |

### Environment

|                         |  |
|-------------------------|--|
| IP degree of protection | IP20   |
| Relative humidity       | 5...90 % non-condensing  |
| Standards               | AS/NZS 3112 safety<br>AS/NZS 60669.2.1 safety<br>AS/NZS 60669.2.1 EMC<br>AS/NZS 4268 radio |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information |  Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |