

Product data sheet

Characteristics

R5042NL-ZW

Wall Plate, C-Bus, Saturn Zen, key input unit, A-Series, 2 key, zen white



Main

Product brand	Clipsal
Range	C-Bus
Product name	C-Bus Saturn Zen A Series
Product or component type	Switch
Device application	Control

Complementary

Device presentation	Basic element with full cover plate
Colour	Zen white
Number of gangs	2 gangs
Control type	Push-button
Provided equipment	Fascia plate Body switch Push-button cap
Material	Plastic
[Ue] rated operational voltage	15...36 V DC
[In] rated current	22 mA
Communication network type	C-Bus
Input impedance	50 kOhm at 1 kHz
Isolation voltage	3.75 kV from C-Bus to mains
Switch function	Load switching Dimmer Time switch function Scene control Roller shutter Bell push switch Curtain
Local signalling	LED (blue/orange) for status
Starting time	5 s
Connections - terminals	Terminal block - 0.2...1.3 mm ² (AWG 24...AWG 16)
Mounting support	Wall box
Fixing center	84 mm
Width	75 mm
Height	118 mm
Depth	25 mm
Net weight	54 g

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	213.0 g
Package 1 Height	70.0 mm
Package 1 width	107.0 mm
Package 1 Length	150.0 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	2.034 kg
Package 2 Height	17.5 cm
Package 2 width	28.0 cm
Package 2 Length	35.0 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	280
Package 3 Weight	66.958 kg
Package 3 Height	122.5 cm
Package 3 width	60.0 cm
Package 3 Length	80.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration