


## Product data sheet

### Characteristics

# R5064VNL

## C-Bus, Reflection Wall Switches, 4 Gang



### Main

Product brand	Clipsal
Device presentation	Basic element with full cover plate


### Complementary

Control type	Button
[Ue] rated operational voltage	15...36 V DC
[In] rated current	20 mA
Mounting support	Wall

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	9 cm
Package 1 Length	13.4 cm
Package 1 Weight	231 g
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	23.5 cm
Package 2 Width	25.1 cm
Package 2 Length	29.6 cm
Package 2 Weight	6.5 kg

### Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	 <a href="#">End Of Life Information</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.