

Product data sheet

Characteristics

R5068NL

C-Bus, Reflection Wall Switches, 8 Gang



Main

Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Control type	Button
[Ue] rated operational voltage	15...36 V DC
[In] rated current	20 mA
Mounting support	Wall

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	9 cm
Package 1 Length	13.3 cm
Package 1 Weight	227 g
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	23.5 cm
Package 2 Width	25.1 cm
Package 2 Length	29.6 cm
Package 2 Weight	6.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information