

Product data sheet

Characteristics

RMXPC1

Clipsal Resi MAX, Cable Connector 1P+N set of 4



Main

Range	Resi MAX
Product or component type	Connector
Accessory / separate part category	Connection accessory
Quantity per set	Set of 4
Colour	White (RAL 9003)



Complementary

Poles description	1P + N
Mounting mode	Horizontal
[Ie] rated operational current	63 A at 40 °C
Connections - terminals	Screw clamp terminals 1...35 mm ² rigid
Tightening torque	4 N.m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	8.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	48.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	100
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.217 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
