

Product data sheet

Characteristics

RPC315M

Rowco, 1 Switch, IP30, 250V, 15A, 3 Pins, 105 X 80 X 54mm



Main

Range of product	PDL Rowco Metal Protected Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Local signalling	Without light indicator
Material	Die cast aluminium
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	8.4 cm
Package 1 Length	12.5 cm
Package 1 Weight	610.0 g

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes