

## Product data sheet

### Characteristics

# S3015XC-CE

Clipsal Iconic, cover frame, 2 switches & 1 socket, 10 A, hori, crowne



#### Main

Range	Clipsal Iconic
Aesthetic name	Iconic Styl
Product or component type	Cover frame
Colour tint	Crowne (CE)
Type of packing	Polybag
Quantity per set	Set of 10

#### Complementary

Range compatibility	Clipsal Iconic switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	2
Number of power socket outlets	1
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Satin
Surface treatment	Metallic
Material	Anodised aluminium: cover frame
Height	82.0 mm
Width	126.0 mm
Depth	8.5 mm
Net weight	0.03 kg

#### Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	8.17 cm
Package 1 Length	12.62 cm
Package 1 Weight	52.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>