

## Product data sheet

### Characteristics

# S3042C-CE

## Skin Switch Iconic Styl - 2-gang - Crpwme



### Main

Range	Clipsal Iconic
Aesthetic name	Iconic Styl
Product or component type	Cover frame
Colour tint	Crowne (CE)
Type of packing	Polybag
Quantity per set	Set of 10

### Complementary

Range compatibility	switch
Product destination	Switch
Device mounting	Flush
Number of rocker	2
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Satin
Surface treatment	Metallic
Material	Anodised aluminium: cover frame
Height	126.0 mm
Width	82.0 mm
Depth	8.5 mm
Net weight	0.03 kg



### Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Package 1 Weight	0.052 kg
Package 1 Height	10.000 mm
Package 1 width	81.700 mm
Package 1 Length	126.200 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 <a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>