

## Product data sheet

### Characteristics

# SAU2505643NDF

Acti9, SAU Chassis, Acti9, 250A, 3Ph+N, 56 poles, 18mm for iC60 MCB and RCBO, dual feed

#### Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

#### Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P + N
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	56
Number of poles	56 x 18 mm
Width	215 mm
Length	506 mm
Busbar pitch	18 mm
Location of connection	Dual feed

#### Environment

Standards	AS/NZS 61439
-----------	--------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	79 cm
Package 1 Weight	5.2 kg