


## Product data sheet

### Characteristics

# SAU25072273

Acti9, SAU Chassis, Acti9, 250A, 3Ph, 72 poles, 27mm for C120 MCB, top or bottom



### Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

### Complementary

Range compatibility	Acti 9 distribution board
Network type	AC
[In] rated current	250 A
Number of ways	1 way (incomer) - 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	72
Number of poles	72 x 27 mm
Width	215 mm
Length	974 mm
Busbar pitch	27 mm
Location of connection	Top or bottom

### Environment

Standards	AS/NZS 61439
-----------	--------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	116.6 cm
Package 1 Weight	7.5 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>