

Product data sheet

Characteristics

SAU40018273DF

SAU Chassis 3PH, Acti9, 400A, 27mm for
C120 MCB, 18 Poles, Dual Feed



Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

Complementary

Incomer device	Switch disconnecter - 3P MCCB - 3P
Protection device type	Miniature circuit breaker (MCB) as outgoing
Network type	AC
[In] rated current	400 A
Number of ways	1 way (incomer) - 3P 1 way (outgoing) - 1P or 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	18
Number of poles	18 x 27 mm
Width	245 mm
Length	529 mm
Depth	95 mm
Product weight	3.0 kg
Busbar pitch	27 mm
Location of connection	Dual feed

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	52.9 cm
Package 1 Weight	2.7 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes