

Product data sheet

Characteristics

SAU40024273DF

SAU Chassis 3PH, Acti9, 400A, 27mm for
C120 MCB, 24 Poles, Dual Feed



Main

| | |
|---------------------------|--------------|
| Range | Acti9 |
| Product or component type | Chassis |
| Device application | Distribution |

Complementary

| | |
|--|--|
| Incomer device | Switch disconnecter - 3P MCCB - 3P |
| Protection device type | Miniature circuit breaker (MCB) as outgoer |
| Network type | AC |
| [In] rated current | 400 A |
| Number of ways | 1 way (incomer) - 3P 1 way (outgoer) - 1P or 3P |
| Rated voltage | 415 V 50 Hz |
| Short-circuit withstand | 25 kA 0.1 s |
| [Ui] rated insulation voltage | 500 V |
| [Uimp] rated impulse withstand voltage | 6 kV |
| Number of poles | 24 |
| Number of poles | 24 x 27 mm |
| Width | 245 mm |
| Length | 610 mm |
| Depth | 95 mm |
| Net weight | 3.6 kg |
| Busbar pitch | 27 mm |
| Location of connection | Dual feed |

Environment

| | |
|-----------|--------------|
| Standards | AS/NZS 61439 |
|-----------|--------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.5 cm |
| Package 1 Width | 24.5 cm |
| Package 1 Length | 61 cm |
| Package 1 Weight | 3.3 kg |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |