


## Product data sheet

### Characteristics

# SAU40036183DF

Acti9, SAU Chassis 3PH 400A, 18mm for iC60 MCB & RCBO, 36 Poles, Dual Feed



### Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

### Complementary

Incomer device	Switch disconnecter - 3P MCCB - 3P
Protection device type	Miniature circuit breaker (MCB) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) as outgoer
Network type	AC
[In] rated current	400 A
Number of ways	1 way (incomer) - 3P 1 way (outgoer) - 1P or 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	36
Number of poles	36 x 18 mm
Width	245 mm
Length	610 mm
Depth	95 mm
Net weight	3.6 kg
Busbar pitch	18 mm
Location of connection	Dual feed

### Environment

Standards	AS/NZS 61439
-----------	--------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	61 cm
Package 1 Weight	3.3 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>