


Product data sheet

Characteristics

SAU40036273

SAU Chassis 3PH, Acti9, 400A, 27mm for C120 MCB, 36 Poles, Top or Bottom Feed



Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

Complementary

Incomer device	Switch disconnecter - 3P MCCB - 3P
Protection device type	Miniature circuit breaker (MCB) as outgoer
Network type	AC
[In] rated current	400 A
Number of ways	1 way (incomer) - 3P 1 way (outgoer) - 1P or 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	36
Number of poles	36 x 27 mm
Width	245 mm
Length	680 mm
Depth	95 mm
Net weight	4.56 kg
Busbar pitch	27 mm
Location of connection	Top or bottom

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	67 cm
Package 1 Length	25 cm
Package 1 Weight	3.89 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes