

Product data sheet

Characteristics

SAU40096183

SAU Chassis 3PH, Acti9, 400A, 18mm for iC60
MCB & RCBO, 96 Poles, Top or Bottom Feed



Main

Range	Acti9
Product or component type	Chassis
Device application	Distribution

Complementary

Incomer device	Switch disconnecter - 3P MCCB - 3P
Protection device type	Miniature circuit breaker (MCB) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) as outgoer
Network type	AC
[In] rated current	400 A
Number of ways	1 way (incomer) - 3P 1 way (outgoer) - 1P or 3P
Rated voltage	415 V 50 Hz
Short-circuit withstand	25 kA 0.1 s
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of poles	96
Number of poles	96 x 18 mm
Width	245 mm
Length	1058 mm
Depth	95 mm
Net weight	7.68 kg
Busbar pitch	18 mm
Location of connection	Top or bottom

Environment

Standards	AS/NZS 61439
-----------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.5 cm
Package 1 Length	105.8 cm
Package 1 Weight	6.7 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes