

Product data sheet

Characteristics

SEA9BN16PEV

Acti9, IsoBar B - pan assembly - 16 ways TP + earth + neutral



Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

Complementary

Range compatibility	Acti 9 (Acti9 IsoBar B) distribution board
Provided equipment	Grounding bar Neutral bar DIN rail Mounting plate
[In] rated current	250 A
Incomer device options	4P switch disconnecter 4P terminal block 3P + N RCCB 3P + N MCCB 4P contactor
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	16 ways (outgoer) 1 way (incomer) - 3P + N + E
Outgoer Pole capacity	48 x 18 mm
Length	671 mm
Width	350 mm
Depth	105 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	39.0 cm
Package 1 Length	69.0 cm
Package 1 Weight	6.243 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Height	130.0 cm
Package 2 Width	112.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	164.76 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product