

Product data sheet

Characteristics

SEA9BN24TNA

Acti9, Isobar B - panel fixing pan assembly - 24 ways TP&N



Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

Complementary

Range compatibility	Acti 9 Acti9 Isobar B distribution board
Provided equipment	Mounting plate
[In] rated current	250 A
Incomer device options	3P switch disconnecter 3P terminal block 3P MCCB
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	1 way (incomer) - 3P + N 24 ways (outgoer)
Outgoer Pole capacity	72 x 18 mm
Length	722 mm
Width	210 mm
Depth	90 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	73.000 cm
Package 1 Length	22.000 cm
Package 1 Weight	9.465 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	56
Package 2 Height	112.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	541.530 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product