

## Product data sheet

### Characteristics

# SEA9BN24TNA

Acti9, IsoBar B - panel fixing pan assembly - 24 ways TP&N



### Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

### Complementary

Range compatibility	Acti 9 (Acti9 IsoBar B) distribution board
Provided equipment	Mounting plate
[In] rated current	250 A
Incomer device options	3P switch disconnecter 3P terminal block 3P MCCB
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	1 way (incomer) - 3P + N 24 ways (outgoer)
Outgoer Pole capacity	72 x 18 mm
Length	722 mm
Width	210 mm
Depth	90 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	73.000 cm
Package 1 Length	22.000 cm
Package 1 Weight	9.465 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	56
Package 2 Height	112.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	541.530 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product