

## Product data sheet

### Characteristics

# SEA9BN6TNA

Acti9, IsoBar B - panel fixing pan assembly - 6 ways TP&N



#### Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution





#### Complementary

Range compatibility	Acti 9 (Acti9 IsoBar B) distribution board
Provided equipment	Mounting plate
[In] rated current	250 A
Incomer device options	3P switch disconnecter 3P terminal block 3P MCCB
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	1 way (incomer) - 3P + N 6 ways (outgoer)
Outgoer Pole capacity	18 x 18 mm
Length	236 mm
Width	210 mm
Depth	90 mm

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	21.0 cm
Package 1 Length	21.5 cm
Package 1 Weight	1.625 kg

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

---

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

---