

## Product data sheet

### Characteristics

# SEA9BN8TNA

Acti9, Isobar B -panel fixing pan assembly - 8 ways TP&N



### Main

Range	Acti9
Product or component type	Pan assembly
Device application	Distribution

### Complementary

Range compatibility	Acti9 (Acti9 Isobar B) distribution board
Provided equipment	Mounting plate
[In] rated current	250 A
Rated voltage	415 V AC 50/60 Hz
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Incomer device options	3P switch disconnecter 3P terminal block 3P MCCB
Protection device options at outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number of ways	8 ways (outgoer) 1 way (incomer) - 3P + N
Outgoer Pole capacity	24 x 18 mm
Busbar pitch	18 mm
Length	290 mm
Width	210 mm
Depth	90 mm

### Environment

Standards	IEC 61439
-----------	-----------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.500 cm
Package 1 Width	22.000 cm
Package 1 Length	30.000 cm
Package 1 Weight	1.875 kg
Unit Type of Package 2	PAL

Number of Units in Package 2	120
Package 2 Height	100.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	245.000 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product