

## Product data sheet

### Characteristics

# SEA9NB12

## Acti9, Isobar B - neutral bar - 1N - for distribution board - 12 ways



### Main

|                           |             |
|---------------------------|-------------|
| Range                     | Acti9       |
| Product or component type | Neutral bar |
| Enclosure type            | Standard    |
| Door type                 | Overall     |

### Complementary

|                                |  |
|--------------------------------|--|
| [Ie] rated operational current | 250 A at 400/415 V AC  |
| Breaking capacity              | 25 kA  |
| Poles description              | 3P + N   |
| Protection device name         | IC60H  |
| Product destination            | Distribution board   |
| Number of ways                 | 12 ways outgoer  |
| Provided equipment             | Neutral bar<br>Busbar link 4<br>Cover  |
| Enclosure material             | Steel  |
| Surface treatment              | Epoxy  |
| Surface finish                 | Powder paint   |
| IP degree of protection        | IP2X internal conforming to BS EN 60529<br>IP3x external conforming to BS EN 60529 |
| IK degree of protection        | IK05 conforming to BS EN 60529   |
| Colour                         | White (RAL 9001)   |
| Height                         | 700 mm   |
| Depth                          | 139 mm   |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -35...70 °C |
| Ambient air temperature for storage   | -40...80 °C |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 8.0 cm  |
| Package 1 Width              | 8.5 cm  |
| Package 1 Length             | 38.0 cm |
| Package 1 Weight             | 387.0 g |
| Unit Type of Package 2       | PAM     |
| Number of Units in Package 2 | 396     |

|                  |            |
|------------------|------------|
| Package 2 Height | 112.0 cm   |
| Package 2 Width  | 100.0 cm   |
| Package 2 Length | 120.0 cm   |
| Package 2 Weight | 197.348 kg |

## Offer Sustainability

|                             |  |
|-----------------------------|--|
| Sustainable offer status    | Green Premium product  |
| REACH Regulation            | <a href="#">REACH Declaration</a>  |
| EU RoHS Directive           | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| China RoHS Regulation       | <a href="#">China RoHS Declaration</a>   |
| RoHS exemption information  | <a href="#">Yes</a>  |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a>  |
| Halogen content performance | Halogen free plastic parts product   |