

## Product data sheet

### Characteristics

# SEA9NB16

## Acti9 DB, Isobar B, neutral bar, 1N, for distribution board, 16 ways



### Main

Product or component type	Neutral bar
Enclosure type	Standard
Door type	Overall

### Complementary

[Ie] rated operational current	250 A at 400/415 V AC
Breaking capacity	25 kA
Poles description	3P + N
Protection device name	IC60H
Product destination	Distribution board
Number of ways	16 ways outgoer
Provided equipment	Neutral bar Busbar link 4 Cover
Enclosure material	Steel
Surface treatment	Epoxy
Surface finish	Powder paint
IP degree of protection	IP2X internal conforming to BS EN 60529 IP3x external conforming to BS EN 60529
IK degree of protection	IK05 conforming to BS EN 60529
Colour	White (RAL 9001)
Height	808 mm
Depth	139 mm

### Environment

Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	8.0 cm
Package 1 Length	71.0 cm
Package 1 Weight	522.0 g
Unit Type of Package 2	PAM
Number of Units in Package 2	200

Package 2 Height	112.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	119.4 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product