

Product data sheet

Characteristics

SEA9NKIT

Acti 9 Isobar P, B type, Isobar A, neutral bar, 1N, for distribution board, 4 ways SP+N



Main

Range of product	Acti9
Product or component type	Neutral bar
Enclosure type	Standard
Enclosure mounting	Wall mounted
Door type	Overall
Enclosure material	Steel
Surface treatment	Epoxy
Surface finish	Powder paint
Poles description	3P + N

Complementary

[Ie] rated operational current	250 A at 230/240 V AC 250 A at 110 V AC
Breaking capacity	25 kA
Protection device name	IC60H
Product destination	Distribution board
Number of ways	4 ways outgoer
Provided equipment	Neutral bar Busbar link 4 Cover
IP degree of protection	IP2X internal conforming to BS EN 60529
IK degree of protection	IK05 conforming to BS EN 60529
Colour	White (RAL 9001)

Environment

Standards	BS EN 60439-3
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	9.800 cm
Package 1 Length	15.600 cm
Package 1 Weight	90.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	22.500 cm
Package 2 Width	28.000 cm
Package 2 Length	34.500 cm
Package 2 Weight	4.600 kg

Unit Type of Package 3	P06
Number of Units in Package 3	800
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	84.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product