

Product data sheet

Characteristics

TC15/15/7D-WE

Single Switch Socket Outlet, 250V, 15A, 7 Day
Timer Control



Main

Range of product	Standard Series
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	42 mm
Length	121 mm
Width	79 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	7.9 cm
Package 1 Length	12.1 cm
Package 1 Weight	0.34 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile