

Product data sheet

Characteristics

TC32V24-WE

Standard Series, Analogue Timer Controls,
Timer Switch 250V 15A - 24 Hour Timer



Main

Product brand	Clipsal
Assembly Type	Basic element with full cover plate

Complementary

[Ue] rated operational voltage	250 V AC
Rated current	15 A
Marking	ON-OFF

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	7.8 cm
Package 1 Length	12.8 cm
Package 1 Weight	230 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	250 cm
Package 2 Width	214 cm
Package 2 Length	338 cm
Package 2 Weight	4.7 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information