

## Product data sheet

### Characteristics

# VW3A8306D30

Altistart 48, Cable for Modbus serial link, 1 x RJ45 and free wires at other end, cable 3 m



### Main

Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part designation	Cable for Modbus serial link
Accessory / separate part destination	Ethernet network XBTGT terminal Modbus bus serial line Soft stop unit Twido PC programming terminal
Range compatibility	TeSys U Harmony XBT Twido Advantys OTB Lexium SD3 Altistart Altivar
Cable length	3 m
Electrical connection	1 male connector RJ45 Free end

### Complementary

Net weight	0.15 kg
------------	---------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	13.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	103.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	40
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.750 kg
Unit Type of Package 3	P06
Number of Units in Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	47.484 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------