

## Product data sheet

### Characteristics

# VW3A9921

## Altivar 32, Kit mechanical adaptor for direct circuit breaker mounting GV2AF5



### Main

Range of product	Altivar
Product or component type	Mounting kit
Accessory / separate part category	Mounting and fixing accessory
Product compatibility	Variable speed drive ATV320...B, 0.18...2.2 kW, 200...240 V, single phase Variable speed drive ATV320...B, 0.37...4 kW, 380...500 V, three phase Variable speed drive ATV32, 0.18...2.2 kW, 200...240 V, single phase Variable speed drive ATV32, 0.37...4 kW, 380...500 V, three phase
Accessory / separate part destination	GV2 circuit-breaker

### Complementary

Kit composition	Adaptor plate
Sale per indivisible quantity	10
Net weight	0.075 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	4.5 cm
Package 1 Length	13.5 cm
Package 1 Weight	88 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7.5 cm
Package 2 Width	17 cm
Package 2 Length	23 cm
Package 2 Weight	895 g
Unit Type of Package 3	S06
Number of Units in Package 3	500
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	56.25 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------