

Product data sheet

Characteristics

WHA110-RG

SWITCH 1 GANG 1 POLE H/PROOF 250V 10A



Main

Range of product	Weathershield
Product brand	Clipsal
Device presentation	Basic element with complete housing

Complementary

Switch function	1-pole
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	ON-OFF
Marking location	Marking on surface




Environment

Standards	AS 60529 AS/NZS 60947-3 IEC 60669-1 AS/NZS 3947-3:approval number S/1
-----------	--

Packing Units

Package 1 Weight	235.000 g
Package 1 Height	88.000 mm
Package 1 width	88.000 mm
Package 1 Length	88.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
