

Product data sheet

Characteristics

WHA116-RG

Weathershield, Surface Switch, 1 Gang, 1 Pole, 250VAC, 16A, Hoseproof, M80 Rating



Main

Range of product	Weathershield
Product brand	Clipsal
Device presentation	Basic element with complete housing

Complementary

Switch function	1-pole
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	16 A
Marking	ON-OFF
Marking location	Marking on surface



Environment

Standards	AS 60529 AS/NZS 60947-3 IEC 60669-1 AS/NZS 3947-3:approval number S/1
-----------	--------------------------------------------------------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	235.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
