

## Product data sheet

### Characteristics

# WHB140-RG

## Weathershield, Surface Switch, 1 Gang, 1 Pole, 250VAC, 40A, Hoseproof, M220 Rating



### Main

Range of product	Weathershield
Product brand	Clipsal
Device presentation	Basic element with complete housing

### Complementary

Switch function	1-pole
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	40 A
Marking	ON-OFF
Marking location	Marking on surface



### Environment

Standards	AS 60529 AS/NZS 60947-3 IEC 60669-1 AS/NZS 3947-3:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	9.2 cm
Package 1 Length	16.8 cm
Package 1 Weight	440.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---