

Product data sheet

Characteristics

WHC363-RG

Weathershield, Switch, 1-Gang, 3 Pole, 63A, 415VAC, IP66



Main

Range of product	Weathershield
Product brand	Clipsal
Device presentation	Basic element with complete housing

Complementary

Switch function	3-pole
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Surface finish	Brilliant
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	63 A
Marking	ON-OFF
Marking location	Marking on surface



Environment

Standards	AS 60529 AS/NZS 60947-3 IEC 60669-1 AS/NZS 3947-3:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	12.0 cm
Package 1 Length	23.8 cm
Package 1 Weight	1269.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile