

Product data sheet

Characteristics

WMB510

Metal Clad, Socket Outlet 1 Gang 10A 500V, 5 Round Sockets, IP66, Cast Aluminium Material



Main

Range of product	Wilco
Product brand	Clipsal

Complementary

Device mounting	Surface
Mounting mode	External mounting
[In] rated current	10 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Black
Duration	7 h
Material	Cast aluminium
Socket number	1
Socket-outlet type	Q
Depth	110 mm
Width	115 mm
Height	150 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	11.5 cm
Package 1 Length	15.0 cm
Package 1 Weight	1030.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	9
Package 2 Height	17.4 cm
Package 2 Width	39.2 cm
Package 2 Length	39.2 cm
Package 2 Weight	9270.0 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile