

## Product data sheet

### Characteristics

# WS226/2PB-RG

Weathershield, Switch, Push Button, 2-Gang,  
3A, 240VAC, IP66



#### Main

Range of product	Weathershield
Product or component type	Push-button
Colour	Resistant grey
Product brand	Clipsal
Device presentation	Basic element with full cover plate

#### Complementary

Colour code	RG
Actuator	Push-button
Contacts type and composition	1 NO for contacts close 1 NC for contacts open
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
Marking location	Marking on surface
[Ue] rated operational voltage	440 V AC
Inrush current	10 A
Marking	START-STOP
Mounting position	Horizontal



#### Environment

IP degree of protection	IP66
-------------------------	------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	223.8 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>