

Product data sheet

Characteristics

WS226SSR/3-RG

Clipsal - Sunset Switch, Weathershield Switch,
3-Wire, 240VAC, 10A



Main

Range of product	Weathershield
Product brand	Clipsal
Device presentation	Basic element

Complementary

Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	240 V AC
Rated current	10 A 10 AX, fluorescent lamp
Marking	Without marking




Environment

Standards	AS/NZS 3133 AS/NZS 3100 IEC 60669-2-1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	35.2 cm
Package 1 Length	9.4 cm
Package 1 Weight	0.26 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	18
Package 2 Height	23.7 cm
Package 2 Width	20.3 cm
Package 2 Length	30 cm
Package 2 Weight	5.24 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information