

## Product data sheet

### Characteristics

# WSC227/15-GY

## Weathershield, Socket, Single, Horse Shoe, 15A, 250VAC, IP53



### Main

Range of product	Weathershield
Product brand	Clipsal

### Complementary

Control type	ON/OFF button Sliding type
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	65 mm
Length	102 mm
Width	85 mm
Fixing center	84 mm

### Environment

IP degree of protection	IP54
Standards	AS/NZS 3112:approval number S/1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	10.6 cm
Package 1 Length	9.8 cm
Package 1 Weight	236.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>