

## Product data sheet

### Characteristics

# WSC227/2-RG

Weathershield, Socket, Twin, 10A, 250VAC, IP54



### Main

Range of product	Weathershield
Product brand	Clipsal

### Complementary

Control type	Sliding type ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	115 mm
Width	85 mm
Fixing center	84 mm

### Environment

IP degree of protection	IP54
Standards	AS/NZS 3112:approval number S/1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	9 cm
Package 1 Length	12 cm
Package 1 Weight	275 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	260 cm
Package 2 Width	437 cm
Package 2 Length	450 cm

Package 2 Weight	14.492 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	260 cm
Package 3 Width	440 cm
Package 3 Length	450 cm
Package 3 Weight	14.55 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>