

## Product data sheet

### Characteristics

# WSC227F2X-RG

## SWITCHED SOCKET TWIN 10A 250V EXTRA SWITCH



### Main

Colour	Resistant grey
Product brand	Clipsal
Range of product	Weathershield

### Complementary

Colour code	RG
Control type	ON/OFF button Sliding type
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	115 mm
Width	85 mm
Fixing center	84 mm

### Environment

IP degree of protection	IP54
Standards	AS/NZS 3112:approval number S/1

### Packing Units

Package 1 Weight	304.000 g
Package 1 Height	86.000 mm
Package 1 width	90.000 mm
Package 1 Length	124.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>