

Product data sheet

Characteristics

WSF226/20-RG

Weathershield, Switch, Flush, 1-Gang,
20A/16AX, 250VAC, IP66



Main

Range of product	Series WSF Weathershield
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	1-way 2-way
Device mounting	Flush
Fixing mode	By screws
Surface finish	Brilliant
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A
Load type	Fluorescent 16 A LEDi lamp 250 W



Environment

Standards	AS/NZS 3133 AS 60529 IEC 60669-1:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	8.8 cm
Package 1 Length	12.0 cm
Package 1 Weight	186.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
