

Product data sheet

Characteristics

ZARC01

Harmony eXLhoist, Charger for remote device, standard



Main

Range of product	Harmony eXLhoist
Accessory / separate part type	Battery charger
Accessory / separate part categor	Electrical accessory

Complementary

[Us] rated supply voltage	100...240 V AC
Network frequency	50...60 Hz
Nominal output current	0.9 A at 90 V AC
Connections - terminals	5-position plug-in connector
Net weight	0.26 kg



Environment

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	7.500 cm
Package 1 Length	14.000 cm
Package 1 Weight	283.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.072 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins