

Product data sheet

Characteristics

ZARC05

Connector plug female, Harmony eXLhoist, standard, with cable 1.5m for ZARB12H

Main

Range of product	Harmony eXLhoist
Accessory / separate part type	Pre-wired connector
Accessory / separate part category	Connection accessory



Complementary

Product compatibility	Control station ZARB
Cable composition	8 x 2.8 mm ² + 40 x 1.5 mm ²
Cable length	1.5 m
Material	PE (polyethylene)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	29.0 cm
Package 1 Length	29.0 cm
Package 1 Weight	1.662 kg
Unit Type of Package 2	S03
Number of Units in Package 2	5
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.836 kg

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
SCIP Number	6e438e59-42d1-4633-bfe2-cb5ef607659b
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No