

Product data sheet

Characteristics

ZARC12

Harmony eXLhoist, Connector plug female, standard, cable 3m for ZARB12H



Main

Range of product	Harmony eXLhoist
Accessory / separate part type	Pre-wired connector
Accessory / separate part category	Connection accessory

Complementary

Product compatibility	Control station ZARB
Pin number	62
Total number of wires	48
Cable composition	8 x 2.8 mm ² + 40 x 1.5 mm ²
Cable length	3 m
Material	PE (polyethylene)
Net weight	3.6 kg

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...60 °C
IP degree of protection	IP65
NEMA degree of protection	NEMA 4

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	29.000 cm
Package 1 Length	39.000 cm
Package 1 Weight	3.030 kg
Unit Type of Package 2	S03
Number of Units in Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.418 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins