

10MDP15-WE

Standard Series, Automatic Single Socket
Outlet Mechanism, 250VAC, 15A, 2 Pole,
Panel Mount



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing
Socket additional information	With hinged lid

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Depth	33 mm
Length	43 mm
Width	42 mm
Fixing center	84 mm
Number of poles	2

Environment


Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.4 cm
Package 1 Length	4.3 cm
Package 1 Weight	52 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.8 cm
Package 2 Width	8.4 cm
Package 2 Length	10.8 cm
Package 2 Weight	280 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50

Package 3 Height	11.7 cm
Package 3 Width	25 cm
Package 3 Length	31 cm
Package 3 Weight	2.8 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration