



### Main

Range of product	Thorsman
Product or component type	Hammer fixing
Product name	Thorsman THI
Device short name	THI
Provided equipment	Screw
Device application	High load installation in board material

### Complementary

Colour tint	Transparent
Practical load capacity	Pull-out load: 350 N for concrete B25 Pull-out load: 250 N for brick Pull-out load: 200 N for sandstone
Practical load capacity	Pull-out load: 35 kg for concrete B25 Pull-out load: 25 kg for brick Pull-out load: 20 kg for sandstone
Ambient air temperature for operation	-40...70 °C
Diameter	5 mm
Length	50 mm

### Environment

Quantity per set	Set of 100
Sale per indivisible quantity	100

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations