



### Main

Range of product	Thorsman
Product or component type	Nail plug
Product name	Thorsman THI
Device short name	THI
Provided equipment	Screw
Device application	High load installation in board material

### Complementary

Colour tint	Transparent
Practical load capacity	Pull-out load: 500 N for concrete B25 Pull-out load: 400 N for brick Pull-out load: 300 N for sandstone
Practical load capacity	Pull-out load: 50 kg for concrete B25 Pull-out load: 40 kg for brick Pull-out load: 30 kg for sandstone
Ambient air temperature for operation	-40...70 °C
Diameter	6 mm
Length	50 mm

### Environment



Quantity per set	Set of 100
Sale per indivisible quantity	100

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	1 cm
Package 1 Length	7.8 cm
Package 1 Weight	5 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
<b>Contractual warranty</b>	
Warranty	18 months