



## Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Distribution Metering
Targeted country	New South Wales

## Complementary

Enclosure mounting	Surface Semi flush
Provided equipment	Enclosure Removable meter panel
Function available	Cable protection slide Clips lead retainer
Protection device type	Miniature circuit breaker (MCB) - 63 A - 2P - 6 kA
Cable entry	Knock-out rear and bottom
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Width	470 mm
Height	680 mm
Depth	280 mm

## Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

## Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--