

Main

Product brand	Clipsal
Optic fiber type	Single mode
Colour	Aqua

Complementary

Optic fiber diameter	62.5/125 µm
Fibre performance	OM1
Diameter	9.1 mm
Bending radius	>= 180 mm
Crush resistance	1800 N/m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.058 kg