



Main

Product brand	Clipsal
Range of product	Actassi
Colour	External sheath: black

Complementary

Diameter	0.4 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	4
Type of cable	2 pairs with 4 conductor(s) stranded
Cable insulation material	PE (polyethylene)
External diameter	5.4 mm

Environment

Environmental characteristic	Water resistant (radially)
Ambient air temperature for operation	-10...70 °C
Standards	AS/ACIF TS008 AS 1049-1 AS 1049-2 AS/NZS 1125

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.