



## Main

Product brand	Clipsal
Range of product	Actassi
Colour	External sheath: black

## Complementary

Diameter	0.64 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	4
Type of cable	2 pairs with 4 conductor(s) stranded
Cable insulation material	Nylon PE (polyethylene)
External diameter	6.5 mm

## Environment

Environmental characteristic	Water resistant (radially)
Ambient air temperature for operation	-10...70 °C
Standards	AS/ACIF TS008 AS/NZS 1125 AS 1049-1 AS 1049-2

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.039 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations