



### Main

|                           |                |
|---------------------------|----------------|
| Range                     | Clipsal Iconic |
| Aesthetic name            | Iconic         |
| Product or component type | Cover frame    |
| Colour tint               | Warm grey (WY) |
| Type of packing           | Polybag        |
| Quantity per set          | Set of 20      |

### Complementary

|                                |   |
|--------------------------------|---|
| Range compatibility            | Switched socket   |
| Product destination            | Switched socket   |
| Device mounting                | Flush   |
| Number of rocker               | 2   |
| Number of power socket outlets | 2   |
| [In] rated current             | 10 A  |
| Installation direction         | Horizontal  |
| Fixing mode                    | Clip-on   |
| Surface finish                 | Matt  |
| Surface treatment              | Untreated   |
| Material                       | PC (polycarbonate): skin<br>ABS (acrylonitrile butadiene-styrene): skin |
| Height                         | 120 mm  |
| Width                          | 78 mm   |
| Depth                          | 12 mm   |
| Net weight                     | 0.02 kg   |

### Environment

|                                       |           |
|---------------------------------------|-----------|
| Ambient air temperature for operation | 0...45 °C |
| Relative humidity                     | 10...95 % |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations      |